

# Eaton BRCAF120

Catalog Number: BRCAF120

Eaton BR AFCI circuit breaker, Arc fault, 20A, 10 kAIC, Single-pole, 120V, BR, #14-4 AWG Cu/Al, Type BR Loadcenters

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR AFCI circuit breaker	BRCAF120
<b>UPC</b>	<b>Product Length/Depth</b>
786685514338	6 in
<b>Product Height</b>	<b>Product Width</b>
1.25 in	3.5 in
<b>Product Weight</b>	<b>Warranty</b>
0.45 lb	Limited lifetime residential, 1 year commercial
<b>Compliances</b>	<b>Certifications</b>
Federal Specifications Classification W-C375	UL 1699

## Product specifications

### Used with

Type BR Loadcenters

### Special features

Arc fault

### Amperage Rating

20 A

### Voltage rating

120 V

### Interrupt rating

10 kAIC

### Main circuit breaker

BR

### Wire size

#14-4 AWG Cu/Al

### Number of poles

Single-pole

## Resources

### Specifications and datasheets

[Eaton Specification Sheet - BRCAF120](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)