

Eaton BRHX2110

Catalog Number: BRHX2110

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,110 A,22kAIC,Two-pole,120/240V,BRHX,Non-interchangeable,110,Plug-on,BRHX



General specifications

Product Name	Catalog Number
Eaton BR thermal magnetic circuit breaker	BRHX2110
	UPC
	786689041663
Product Length/Depth	Product Height
2.6 in	2 in
Product Width	Product Weight
1.9 in	0.75 lb
Warranty	Certifications
1 year	Contact Manufacturer

Product specifications

Type

Quicklag Type BRHX circuit breaker

Amperage Rating

110

Voltage rating

120/240 V

Trip Type

Non-interchangeable

Circuit breaker type

BR

Mounting Method

Plug-on

Interrupt rating

22 kAIC

Main circuit breaker

BR

Connection

Plug-on

Number of poles

Two-pole

Trip rating

110 A

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRHX2110](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)