

# Eaton BRHX2125

Catalog Number: BRHX2125

Eaton BR thermal magnetic circuit breaker,Quicklag Type BRHX circuit breaker,125 A,22kAIC,Two-pole,120/240V,BRHX,Non-interchangeable,125,Plug-on,BRHX



## General specifications

|   |                       |
|---|-----------------------|
| <b>Product Name</b>                       | <b>Catalog Number</b> |
| Eaton BR thermal magnetic circuit breaker | BRHX2125              |
|   | UPC                   |
|   | 786689041670          |
| <b>Product Length/Depth</b>               | <b>Product Height</b> |
| 3.1 in                                    | 3 in                  |
| <b>Product Width</b>                      | <b>Product Weight</b> |
| 2.2 in                                    | 0.9 lb                |
| <b>Warranty</b>                           | <b>Certifications</b> |
| 1 year                                    | Contact Manufacturer  |

## Product specifications

### Type

Quicklag Type BRHX circuit breaker

### Amperage Rating

125

### Voltage rating

120/240 V

### Trip Type

Non-interchangeable

### Circuit breaker type

BR

### Mounting Method

Plug-on

### Interrupt rating

22 kAIC

### Main circuit breaker

BR

### Connection

Plug-on

### Number of poles

Two-pole

### Trip rating

125

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRHX2125](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)