

# Eaton BRP12B100R

Catalog Number: BRP12B100R

Plug-on neutral main circuit breaker loadcenter, 125A, X1, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, 24 circuits, Single pole, 12 spaces, Three-wire, Single-phase, Combination, NEMA 3R, Type BR 1-inch breakers, 120/240V

## General specifications



Photo is representative

<b>Product Name</b>	<b>Catalog Number</b>
Eaton BR main breaker loadcenter	BRP12B100R
<b>UPC</b>	<b>Product Length/Depth</b>
786689059149	18.75 in
<b>Product Height</b>	<b>Product Width</b>
5.5 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15 lb	10 year
<b>Certifications</b>	
UL 50	
UL 67	

## defaultTaxonomyAttributeLabel

### Type

Plug-on neutral main circuit breaker loadcenter

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Number of circuits

24

### Number Of Poles

Single-pole

### Number of spaces

12

### Phase

Single-phase

### Mounting

Combination

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X1

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

### Number of wires

3

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP12B100R

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

NEMA rating

NEMA 3R

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)