

Eaton BRP12L200R

Catalog Number: BRP12L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, Single-pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V



General specifications

| | |
|------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main lug loadcenter | BRP12L200R |
| UPC | Product Length/Depth |
| 786689059163 | 3.88 in |
| Product Height | Product Width |
| 18.75 in | 14.31 in |
| Product Weight | Warranty |
| 15 lb | 10 year |

Certifications

UL 67
UL 50

Product specifications

Type

MLO

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12L200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP12L200R

Catalog Number: BRP12L200R

Eaton Eaton BR main lug loadcenter, Main lug only, 200 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 24 Circuits, Single-pole, 12 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V



General specifications

| | |
|------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main lug loadcenter | BRP12L200R |
| UPC | Product Length/Depth |
| 786689059163 | 3.88 in |
| Product Height | Product Width |
| 18.75 in | 14.31 in |
| Product Weight | Warranty |
| 15 lb | 10 year |

Certifications

UL 67
UL 50

Product specifications

Type

MLO

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

24

Number Of Poles

Single-pole

Number of spaces

12

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP12L200R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)