

Eaton BRP16B125

Catalog Number: BRP16B125

Plug-on neutral main circuit breaker loadcenter, 125A, X2, Aluminum, Cover included, NEMA 1, Metallic, 10kAIC, BR2125, 32 circuits, Single pole, 16 spaces, Two hots, a neutral, and a ground, Single-phase, Gray, Combination, NEMA 1, Type BR 1-inch breakers, 1



Photo is representative

General specifications

| | |
|----------------------------------|-----------------------------|
| Product Name | Catalog Number |
| Eaton BR main breaker loadcenter | BRP16B125 |
| UPC | Product Length/Depth |
| 786689053086 | 21 in |
| Product Height | Product Width |
| 3.88 in | 14.31 in |
| Product Weight | Warranty |
| 19.5 lb | 10 year |
| Certifications | |
| UL 67 | |
| UL 50 | |

defaultTaxonomyAttributeLabel

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2125

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Enclosure color

Gray

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X2

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - BRP16B125

Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground

NEMA rating

NEMA 1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)