

# Eaton BRP16L125

Catalog Number: BRP16L125

Eaton Eaton BR main lug loadcenter,Main lug only,125 A,X1,Aluminum,Gray, NEMA 1,Metallic,10kAIC,BR2125,Surface,flush,32 Circuits,Twenty-four pole,16 Spaces,Two hots,a neutral,and a ground,Single-phase,120/240V,#6-2/0 AWG Cu/Al



## General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP16L125
UPC	Product Length/Depth
786689053116	18.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
18.8 lb	10 year
Certifications	
UL 67	
UL 50	

## Product specifications

### Type

MLO

### Amperage Rating

125 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR2125

### Mounting

Surface, flush

### Number of circuits

32

### Number Of Poles

Single-pole

### Number of spaces

16

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240V

### Box size

X1

### Color

Gray

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

[Loadcenters and Circuit Breakers](#)

### Specifications and datasheets

[Eaton Specification Sheet - BRP16L125](#)

### Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)