

Eaton BRP16L125R

Catalog Number: BRP16L125R

Eaton Eaton BR main lug loadcenter, Main lug only, 125 A, X1, Aluminum, NEMA 3R, Metallic, 10 kAIC, BR, NEMA 3R, 32 Circuits, Single-pole, 16 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240V, #6-2/0



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP16L125R
UPC	Product Length/Depth
786689059200	3.88 in
Product Height	Product Width
18.75 in	14.31 in
Product Weight	Warranty
15 lb	10 year

Certifications

UL 67
UL 50

Product specifications

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Box size

X1

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 3R

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP16L125R](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia