

# Specifications

## Eaton BRP20N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V

### General specifications

<b>PRODUCT NAME</b>	Eaton BR convertible loadcenter
<b>CATALOG NUMBER</b>	BRP20N200G
<b>UPC</b>	786689053307
<b>PRODUCT LENGTH/DEPTH</b>	29.12 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	27 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67

## Product specifications

<b>SPECIAL FEATURES</b>	Ground bar
<b>TYPE</b>	Convertible
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>MOUNTING</b>	Combination
<b>NUMBER OF CIRCUITS</b>	40
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	X5
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	Two hots, neutral and ground

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BRP20N200G</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton BRP20N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V

### General specifications

<b>PRODUCT NAME</b>	Eaton BR convertible loadcenter
<b>CATALOG NUMBER</b>	BRP20N200G
<b>UPC</b>	786689053307
<b>PRODUCT LENGTH/DEPTH</b>	29.12 in
<b>PRODUCT HEIGHT</b>	3.88 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	27 lb
<b>WARRANTY</b>	10 year
<b>CERTIFICATIONS</b>	UL 50 UL 67

## Product specifications

<b>SPECIAL FEATURES</b>	Ground bar
<b>TYPE</b>	Convertible
<b>AMPERAGE RATING</b>	200 A
<b>BUS MATERIAL</b>	Aluminum
<b>COVER</b>	Cover included
<b>MAIN CIRCUIT BREAKER</b>	CSR
<b>MOUNTING</b>	Combination
<b>NUMBER OF CIRCUITS</b>	40
<b>NUMBER OF POLES</b>	Single-pole
<b>NUMBER OF SPACES</b>	20
<b>PHASE</b>	Single-phase
<b>USED WITH</b>	Type BR 1-inch breakers
<b>VOLTAGE RATING</b>	120/240 V
<b>BOX SIZE</b>	X5
<b>ENCLOSURE</b>	NEMA 1
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	10 kAIC
<b>NUMBER OF WIRES</b>	Two hots, neutral and ground

## Resources

<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - BRP20N200G</a>
<b>WARRANTY GUIDES</b>	<a href="#">Eaton type BR circuit breaker limited warranty June 2024</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

