

# Eaton BRP20N200G

Catalog Number: BRP20N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



## General specifications

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Name</b>             | <b>Catalog Number</b>       |
| Eaton BR convertible loadcenter | BRP20N200G                  |
| <b>UPC</b>                      | <b>Product Length/Depth</b> |
| 786689053307                    | 29.12 in                    |
| <b>Product Height</b>           | <b>Product Width</b>        |
| 3.88 in                         | 14.31 in                    |
| <b>Product Weight</b>           | <b>Warranty</b>             |
| 27 lb                           | 10 year                     |
| <b>Certifications</b>           |                             |
| UL 50                           |                             |
| UL 67                           |                             |

## defaultTaxonomyAttributeLabel

### Special features

Ground bar

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

CSR

### Mounting

Combination

### Number of circuits

40

### Number Of Poles

Single-pole

### Number of spaces

20

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X5

### Enclosure

NEMA 1

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Brochures

Loadcenters and Circuit Breakers

### Specifications and datasheets

Eaton Specification Sheet - BRP20N200G

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024

Number of wires

Two hots, neutral and ground



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://Eaton.com/socialmedia)