

Eaton BRP20N200G

Catalog Number: BRP20N200G

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 1, Metallic, 10 kAIC, CSR, Combination, 40 Circuits, Single-pole, 20 Spaces, Two hots, neutral, and a ground, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

Product Name	Catalog Number
Eaton BR convertible loadcenter	BRP20N200G
UPC	Product Length/Depth
786689053307	29.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
27 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Special features

Ground bar

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR

Mounting

Combination

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Specifications and datasheets

[Eaton Specification Sheet - BRP20N200G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)