

Eaton BRP20N200RG

Catalog Number: BRP20N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP20N200RG |
| UPC | Product Length/Depth |
| 786689059309 | 3.88 in |
| Product Height | Product Width |
| 29.13 in | 14.31 in |
| Product Weight | Warranty |
| 19 lb | 10 year |

Certifications

UL 67
UL 50

Product specifications

Special features

Ground bar

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20N200RG](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP20N200RG

Catalog Number: BRP20N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X5, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 40 Circuits, Single-pole, 20 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



General specifications

| | |
|---------------------------------|----------------------|
| Product Name | Catalog Number |
| Eaton BR convertible loadcenter | BRP20N200RG |
| UPC | Product Length/Depth |
| 786689059309 | 3.88 in |
| Product Height | Product Width |
| 29.13 in | 14.31 in |
| Product Weight | Warranty |
| 19 lb | 10 year |

Certifications

UL 67
UL 50

Product specifications

Special features

Ground bar

Type

Convertible

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR

Mounting

Combination

Number of circuits

40

Number Of Poles

Single-pole

Number of spaces

20

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP20N200RG](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

3



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)