

Eaton BRP24L125

Catalog Number: BRP24L125

Eaton Eaton BR main lug loadcenter ,Ground bar,Main lug only,125 A,X0,Aluminum,Cover included,NEMA 1,Metallic,10kAIC,BR2125,Surface, flush,NEMA 1,24 Circuits,Twenty-four pole,12 Spaces,Two hots, a neutral



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP24L125
UPC	Product Length/Depth
786689053352	23 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
20 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Type

MLO

Amperage Rating

125 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

BR2125

Mounting

Surface, flush

Number of circuits

48

Number Of Poles

Single-pole

Number of spaces

24

Phase

Single-phase

Used with

Type BR 1-inch breakers

Voltage rating

120/240V

Wire size

#6-1/0 AWG Cu/Al

Box size

X3

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP24L125](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)