

Eaton BRP30B200

Catalog Number: BRP30B200

Eaton BR main breaker loadcenter, includes BREQS125 hold-down screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR2200, 60 circuits, Single pole, 30 spaces



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B200
UPC	Product Length/Depth
786689044060	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
31.1 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30B200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton BRP30B200

Catalog Number: BRP30B200

Eaton BR main breaker loadcenter, includes BREQS125 hold-down screw, Plug-on neutral main circuit breaker loadcenter, 200 A, X6, Aluminum, Cover included, NEMA 1, Metallic, 25 kAIC, CSR2200, 60 circuits, Single pole, 30 spaces



General specifications

Product Name	Catalog Number
Eaton BR main breaker loadcenter	BRP30B200
UPC	Product Length/Depth
786689044060	34.12 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
31.1 lb	10 year
Certifications	
UL 50	
UL 67	

Product specifications

Special features

Ground bar, includes BREQS125 hold-down screw

Type

Plug-on neutral main circuit breaker loadcenter

Amperage Rating

200 A

Bus material

Aluminum

Cover

Cover included

Main circuit breaker

CSR2200

Number of circuits

60

Number Of Poles

Single-pole

Number of spaces

30

Phase

Single-phase

Mounting

Combination

Used with

Type BR 1-inch breakers

Voltage rating

120/240 V

Box size

X6

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP30B200](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Number of wires

Two hots, neutral and ground



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)