


## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST 72712-0000, AR Bentonville Phone: 479-250-1930 Fax: 479-250-1931





**UPC** 

## **BRP30B200RV25 BR Pon Loadcntr 200A Main BRKR 30 Space N3R** Eaton Corp

Eaton Corp	•
Catalog Number	BRP30B200RV25
Manufacturer	Eaton Corp
Description	BR Plug-On Neutral Loadcenter Value Pack, 200A, Main Breaker, 30 Spaces, Nema 3R W/ (2) BR120 & (1) BR230
Weight per unit	·
Product Category	
Features	Single Fridse Main Breaker Load
amperage rating	200
cover Type interrupt rating	
number of spaces	
<u>.</u> .	
Phase Voltage Rating	
	120/240 V
Dimensions and Weight	24.12
Depth	
Height	
Size	
Width	14.31
Descriptions	
Description	BR PON LOADCNTR 200A MAIN BRKR 30 SPACE N3R
extra long description	ETN BRP30B200RV25 BR PON LC,200A, M
Features	Specially designed for easy installation, Eaton's BR 1-inch load centers house the branch circuit breakers and the wiring required to distribute power to individual circuits. They serve as main breaker for service entrances or as main lug when adding circuits to existing service. The main breaker protects the entire panel and can be used as a service disconnect. The branch breakers
	protect the wires leading to individual electrical loads such as fixtures and outlets.
Long Description	BR plug-on neutral loadcenter value pack, 200A, main breaker, 30 spaces, NEMA 3R w/ (2) BR120 & (1) BR230
Product Type	BR Pon LC, 200A, MCB, 30 Space, N3R
Special Features	Value pack
Manufacturer Information	
Brand	Eaton
GTIN	00786689058432
Manufacturers Part Number	BRP30B200RV25

786689058432



standard

## ELLIOTT ELECTRIC SUPPLY 320 SW 28TH ST 72712-0000, AR Bentonville Phone: 479-250-1930 Fax: 479-250-1931

Taxonomies, Classifications, an	nd Categories
Category Description	LOADCENTERS & COVERS
Туре	Main breaker loadcenter
Packaging	
Carton	1
Weight Per each	27
Uses, Certifications, and Standa	ards
Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels
	and EOEMs
Mounting	Combination Mount

UL 50,UL 67