

Specifications



Powering Business Worldwide

Eaton BRP30L200GW

Eaton Eaton BR main lug
loadcenter,Indoor,Main lug only,200
A,X5,Aluminum, NEMA
1,Metallic,10kAIC,CSR2200,Surface,flush,NEMA
1,60 Circuits,Twenty-four pole,30 Spaces,Two
hots,a neutral,and a ground,Single-
phase,120/240V,#1-300 kcmil

General specifications	
PRODUCT NAME	Eaton BR main lug loadcenter
CATALOG NUMBER	BRP30L200GW
UPC	786689052904
PRODUCT LENGTH/DEPTH	29.12 in
PRODUCT HEIGHT	3.88 in
PRODUCT WIDTH	14.31 in
PRODUCT WEIGHT	26.3 lb
WARRANTY	10 year
CERTIFICATIONS	UL 67 UL 50

Product specifications		Resources	
TYPE	MLO	SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BRP30L200GW
AMPERAGE RATING	200 A		
BUS MATERIAL	Aluminum	WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024
COVER	Cover included		
MAIN CIRCUIT BREAKER	CSR2200		
MOUNTING	Surface, flush		
NUMBER OF CIRCUITS	60		
NUMBER OF POLES	Single-pole		
NUMBER OF SPACES	30		
PHASE	Single-phase		
USED WITH	Type BR 1-inch breakers		
VOLTAGE RATING	120/240V		
BOX SIZE	X5		
ENCLOSURE	NEMA 1		
ENCLOSURE MATERIAL	Metallic		
INTERRUPT RATING	10 kAIC		
NEMA RATING	NEMA 1		
NUMBER OF WIRES	Two hots, neutral and ground		

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE:



Eaton Corporation plc
 Eaton House
 30 Pembroke Road
 Dublin 4, Ireland
 Eaton.com

Follow us on social media to get the latest product and support information.

