

# Eaton BRP40N200RG

Catalog Number: BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

## General specifications

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Name</b>             | <b>Catalog Number</b>       |
| Eaton BR convertible loadcenter | BRP40N200RG                 |
| <b>UPC</b>                      | <b>Product Length/Depth</b> |
| 786689059064                    | 3.88 in                     |
| <b>Product Height</b>           | <b>Product Width</b>        |
| 3.88 in                         | 14.13 in                    |
| <b>Product Weight</b>           | <b>Warranty</b>             |
| 27 lb                           | 10 year                     |

## Certifications

UL 50  
UL 67

## Product specifications

### Special features

Ground bar

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

80

### Number Of Poles

Single-pole

### Number of spaces

40

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X8

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Specifications and datasheets

Eaton Specification Sheet - BRP40N200RG

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton BRP40N200RG

Catalog Number: BRP40N200RG

Eaton BR convertible loadcenter, Ground bar, Convertible, 200 A, X8, Aluminum, Cover included, NEMA 3R, Metallic, 10 kAIC, BR, Combination, 80 Circuits, Single-pole, 40 Spaces, Three-wire, Single-phase, Type BR 1-inch breakers, 120/240 V



Photo is representative

## General specifications

|                                 |                             |
|---------------------------------|-----------------------------|
| <b>Product Name</b>             | <b>Catalog Number</b>       |
| Eaton BR convertible loadcenter | BRP40N200RG                 |
| <b>UPC</b>                      | <b>Product Length/Depth</b> |
| 786689059064                    | 3.88 in                     |
| <b>Product Height</b>           | <b>Product Width</b>        |
| 3.88 in                         | 14.13 in                    |
| <b>Product Weight</b>           | <b>Warranty</b>             |
| 27 lb                           | 10 year                     |

## Certifications

UL 50  
UL 67

## Product specifications

### Special features

Ground bar

### Type

Convertible

### Amperage Rating

200 A

### Bus material

Aluminum

### Cover

Cover included

### Main circuit breaker

BR

### Mounting

Combination

### Number of circuits

80

### Number Of Poles

Single-pole

### Number of spaces

40

### Phase

Single-phase

### Used with

Type BR 1-inch breakers

### Voltage rating

120/240 V

### Box size

X8

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

10 kAIC

## Resources

### Specifications and datasheets

Eaton Specification Sheet - BRP40N200RG

### Warranty guides

Eaton type BR circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)