

Eaton BRP42LC225G

Catalog Number: BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, Main lug only, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, Single-pole, 42 Spaces, a neutral and a ground, Single-phase, 1, 120/240V, #6-1/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP42LC225G
UPC	Product Length/Depth
786689055059	39 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
36.3 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Main Lug Only

Type

Main Lug Only

Amperage Rating

225 A

Bus material

Copper

Cover

Cover included

Main circuit breaker

BR

Mounting

Surface, flush

Number of circuits

84

Number Of Poles

Single-pole

Number of spaces

42

Phase

Single-phase

Used with

BR

Voltage rating

120/240V

Wire size

#6-1/0 AWG Cu/Al

Box size

X8

Color

Gray

Enclosure

NEMA 1

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP42LC225G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia

Eaton BRP42LC225G

Catalog Number: BRP42LC225G

Eaton Eaton BR main lug loadcenter, Main Lug Only, Ground bar, Main lug only, 225 A, X8, Copper, Gray, NEMA 1, 10kAIC, BR, Surface, flush, 84 Circuits, Single-pole, 42 Spaces, a neutral and a ground, Single-phase, 1, 120/240V, #6-1/0 AWG Cu/Al



General specifications

Product Name	Catalog Number
Eaton BR main lug loadcenter	BRP42LC225G
UPC	Product Length/Depth
786689055059	39 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
36.3 lb	10 year
Certifications	
UL 67	
UL 50	

defaultTaxonomyAttributeLabel

Special features

Main Lug Only

Type

Main Lug Only

Amperage Rating

225 A

Bus material

Copper

Cover

Cover included

Main circuit breaker

BR

Mounting

Surface, flush

Number of circuits

84

Number Of Poles

Single-pole

Number of spaces

42

Phase

Single-phase

Used with

BR

Voltage rating

120/240V

Wire size

#6-1/0 AWG Cu/Al

Box size

X8

Color

Gray

Enclosure

NEMA 1

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - BRP42LC225G](#)

Warranty guides

[Eaton type BR circuit breaker limited warranty June 2024](#)

Enclosure material

Metallic

Interrupt rating

10 kAIC

NEMA rating

NEMA 1

Number of wires

Two hots, neutral and ground

Quantity

1



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia