



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## BT3IC0 11.3" NylN CBL Tie SS Barb Int Cross Sec BLCK *Panduit Corporation*

|                  |  |
|------------------|--|
| Catalog Number   | BT3IC0   |
| Manufacturer     | Panduit Corporation  |
| Description      | Cable Tie, Nylon 6.6 Material, Black, 11.3 In Length, 3 In Bundle Diameter, 0.141 In Width, Weather Resistant, 0.05 In Thickness, 40 LB Tensile Strength, -76 °F Operating Temperature, +185 °F Operating Temperature, 0.38 LB |
| Weight per unit  | 0.3850 (lbs/each)  |
| Product Category | Cable Ties & Wraps   |

### Features

|       |     |
|-------|-----|
| media | Yes |
|-------|-----|

### Dimensions and Weight

|        |      |
|--------|------|
| Length | 11.3 |
|--------|------|

### Descriptions

|                        |  |
|------------------------|--|
| Description            | 11.3" NYL N CBL TIE SS BARB INT CROSS SEC BLCK |
| extra long description | PAN BT3I-C0 Dome-Top® BT3I-C0 Barb             |
| Special Features       | Indoor/Outdoor                                 |

### Manufacturer Information

|       |                |
|-------|----------------|
| Brand | PANDUIT        |
| GTIN  | 00074983413676 |
| UPC   | 074983413676   |

### Taxonomies, Classifications, and Categories

|                      |  |
|----------------------|--|
| Category Description | Screws, Bolts, Staples, Jack Chains, Washers & TY-Raps |
| Type                 | Cable Tie  |

### Availability

|             |     |
|-------------|-----|
| minimum qty | 100 |
|-------------|-----|

### Packaging

|                 |       |
|-----------------|-------|
| Carton          | 100   |
| Package         | 1000  |
| Weight Per each | 0.385 |

### Uses, Certifications, and Standards

|          |  |
|----------|--|
| standard | UL 62275 (File E56854), CSA-C22.2 No. 62275, 11130200, NRC 10CFR50, QPL-AS23190, CSA Certified, RoHS Compliant |
|----------|--|