

Eaton C0300E5E

Catalog Number: C0300E5E

Eaton Type MTE industrial control transformer, pv: 200/220/440v, 208/230/460v, 240/480v, taps: none, sv: 23/110v, 24/115v, 25/120v, 55°C, 300 va , cu magnet wire

General specifications



Photo is representative

Product Name	Catalog Number
Eaton Type MTE industrial control transformer	C0300E5E
	UPC
	786680420429
Product Length/Depth	Product Height
5.118 in	4.764 in
Product Width	Product Weight
5.236 in	15.5 lb
Warranty	Compliances
Eaton Selling Policy 25-000, one (1) year RoHS Compliant from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	Certifications
	CSA Certified
	UL Listed
	cUL Certified

Catalog Notes

Epoxy encapsulated, Laminations of high quality silicon steel to minimize core losses and optimize performance, 50/60Hz operation, 130°C insulation system standard, Molded-in terminals for maximum durability

Physical Attributes

Coil material

Copper windings

Design

MTE

Tap size

None

Performance Ratings

Primary voltage

200/220/440 V, 208/230/460 V, 240/480 V

Temperature rating

55°C

Volt ampere rating

300 VA

Secondary voltage

23/110 V, 24/115 V, 25/120 V

Resources

Specifications and datasheets

[Eaton Specification Sheet - C0300E5E](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)