



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C10 1/0 Cu Long Barrel Compression Butt Splice

*Nsi Industries*

|                  |  |
|------------------|--|
| Catalog Number   | C10  |
| Manufacturer     | Nsi Industries   |
| Description      | Long Barrel TINNEDCOPPERSPLICE1/0 Awg Long Barrel Tinned Coppersplices Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed. |
| Weight per unit  | 0.1100 (lbs/each)  |
| Product Category | Large Terminals & Connectors   |

### Features

|                      |        |
|----------------------|--------|
| Material             | Copper |
| Number of Conductors | 2      |
| Poles                | 1      |
| Voltage Rating       | 600 V  |
| Warranty             | 1 YEAR |

### Material, Color, and Finish

|        |            |
|--------|------------|
| Color  | Pink       |
| Finish | Tin Plated |

### Dimensions and Weight

|      |                            |
|------|----------------------------|
| Size | L=2.20 - OD=.519 - ID=.389 |
|------|----------------------------|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |  |
|------------------------|--|
| Description            | 1/0 CU LONG BARREL COMPRESSION BUTT SPLICE   |
| extra long description | NSI C-1/0 1/0 AWG Copper Long Barre  |
| Features               | Long Barrel TinnedCopperSplice1/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Long Description       | Long Barrel TinnedCopperSplice1/0 AWG Long Barrel Tinned CopperSplices is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed. |
| Product Type           | 1/0 Awg Copper Long Barrel Splice - Pink   |
| Special Features       | 1/0 AWG (STR) - CU Splice  |

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | NSi            |
| GTIN                      | 00662381037558 |
| Manufacturers Part Number | C-1/0          |
| UPC                       | 662381037558   |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Comp & Mech Lugs and Butt Splices |
| Type                 | Long Barrel - CU Splice           |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 50   |
| Weight Per each | 0.11 |

## Uses, Certifications, and Standards

|                          |   |
|--------------------------|---|
| Application              | Terminate, Splice, Tap Power Connectors |
| environmental conditions | 90 C                                    |
| standard                 | UL486A/B, UL467 (8 AWG -3/0 AWG)        |
| Temperature Rating       | 90 C                                    |