



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196



C232MV *Delisted* 4' 2 LMP Strip Light 32W 120-277V T8

Lithonia Lighting - Acuity

Catalog Number	C232MV
Manufacturer	Lithonia Lighting - Acuity
Description	Strip Light, T8 Bulb Shape, 48 In Length, 4-3/8 In Width, 2-1/8 In Height, 120 to 277 V, 32 W, Electronic Ballast, Instant, White, 2 Lamps, Steel Housing Material, Enamel, Surface Mount, 6.199 LB/Ea
Weight per unit	5.8 (lbs/each)
Product Category	Fluorescent Industrial Lightin

Features

dimensions	48 X 4-3/8 X 2-1/8
Hardware	No
Lamp Included	NO
Lamp Type	Fluorescent
Material	Steel
Maximum Operating Temperature	25
Number of Lamps	2
pallet quantity	99
Shape	Rectangular
Socket Type	Medium: Bi-pin
Warranty	2
Wattage	64

Descriptions

Description	*DELISTED* 4' 2 LMP STRIP LIGHT 32W 120-277V T8
-------------	---

Manufacturer Information

GTIN	00745975079711
UPC	745975079711

Taxonomies, Classifications, and Categories

Category Description	Fluorescent Fixtures & Accessories
Type	Strip Light

Availability

Manufacturer Status	Inactive
---------------------	----------

Packaging

Carton	1
Weight Per each	5.75



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1821 North Topping Avenue
64120-0000, MO Kansas City
Phone: 913-227-4257
Fax: 816-656-2196

Uses, Certifications, and Standards

environmental conditions

Indoor

Mounting
standard

Surface, Suspended
UL