

Specifications



Photo is representative



Eaton C25DNF330C

Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF330C
UPC	782116311361
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.3 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
OPTIONS	Global listed
TYPE	Non-reversing
AUXILIARY CONTACTS	Quick connect (side-by-side)
COIL	440-480 Vac, 50/60 Hz
COIL VOLTAGE	277 Vac, 60 Hz
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactactor
RESISTIVE LOAD	40 A
SERIES	D1
TERMINALS	Box lugs (posidrive setscrew)
CONNECTION	Quick

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - C25DNF330C](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications



Photo is representative



Eaton C25DNF330C

Eaton definite purpose contactor, Quick, 30A, 208-240 Vac at 50/60 Hz, Open with metal mounting plate, 15-50A, two- or 3P, 15-50A, two- and 3P, Contactor, 3P, Global ratings, Box lugs (posidrive setscrew) and quick connect terminals

General specifications

PRODUCT NAME	Eaton definite purpose contactor
CATALOG NUMBER	C25DNF330C
UPC	782116311361
PRODUCT LENGTH/DEPTH	3.35 in
PRODUCT HEIGHT	3.75 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	1.3 lb
WARRANTY	1 year
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL Recognized CSA Certified UL Listed file E1491 (Guide Number NLDX2)



Powering Business Worldwide

Product specifications

AMPERAGE RATING	30A
NUMBER OF POLES	Three-pole
OPTIONS	Global listed
TYPE	Non-reversing
AUXILIARY CONTACTS	Quick connect (side-by-side)
COIL	440-480 Vac, 50/60 Hz
COIL VOLTAGE	277 Vac, 60 Hz
ENCLOSURE	Open with metal mounting plate
FRAME SIZE	15-50 A, two-pole and three-pole
INDUCTIVE FULL LOAD	30 A
MODEL	Contactactor
RESISTIVE LOAD	40 A
SERIES	D1
TERMINALS	Box lugs (posidrive setscrew)
CONNECTION	Quick

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - C25DNF330C](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

