



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C25END430A DP Cont 30A 4P Opn 120V Eaton Corp

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | C25END430A |
| Manufacturer | Eaton Corp |
| Description | Definite Purpose Control - Contactor, 4 Poles, 30 A, 110 to 120 V Ac, 40 A Resistive Load, 3 Phases, 15 HP;11 KW Motor Power, 25 to 40 A Frame, Quick Connect Terminal Connection, -13 °F Operating Temperature, +158 °F Operating Temperature, Din Rail Mount, 50 to 60 HZ, 3.75 In Overall Height, 3.38 In Overall Length, 2.68 In Overall Width, 2.15 LB |
| Weight per unit | 2.2 (lbs/each) |
| Product Category | Definite Purpose Contactors |

Features

| | |
|----------------|--------------------------------|
| Enclosure Type | Open with metal mounting plate |
|----------------|--------------------------------|

Dimensions and Weight

| | |
|--------|------|
| Depth | 3.38 |
| Height | 3.75 |
| Width | 2.68 |

Descriptions

| | |
|------------------------|-------------------------------------|
| Description | DP CONT 30A 4P OPN 120V |
| extra long description | ETN C25END430A DP CONT 30A 4P OPN 1 |

Manufacturer Information

| | |
|-------|----------------|
| Brand | Eaton |
| GTIN | 00782113542331 |
| UPC | 782113542331 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|----------------------------|
| Category Description | DP CONTACTORS |
| Type | Definite purpose contactor |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Weight Per each | 2.15 |

Uses, Certifications, and Standards

| | |
|----------|-----------------------------|
| standard | CSA Certified,UL Recognized |
|----------|-----------------------------|