



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



C320AMH2 Double-Pole Auxiliary Contact

Eaton Corp

Catalog Number	C320AMH2
Manufacturer	Eaton Corp
Description	Eaton C30CN Mechanically Held Lighting Contactor Auxiliary Contacts, Two-Pole
Weight per unit	0.0200 (lbs/each)
Product Category	Contactor Accessories

Features

dimensions	2.0000 IN X 0.5000 IN X 1.5000 IN
------------	-----------------------------------

Dimensions and Weight

Depth	2
Height	1.5
Width	0.5

Descriptions

Description	DOUBLE-POLE AUXILIARY CONTACT
extra long description	ETN C320AMH2 Double-Pole Auxiliary
Features	The C30CN 30A mechanically held lighting contactors are designed for industrial, commercial and outdoor lighting applications where efficient control is required. The mechanically held operation ensures that the contactor will not switch to OFF during control power failure. It also ensures the removal of coil from the circuit for noise-free operation and the elimination of all coil losses after the contactor is latched. The control module microprocessor validates the control signal before operation, so it
Long Description	Eaton C30CN mechanically held lighting contactor auxiliary contacts, two-pole
Product Type	Double-Pole Auxiliary Contact
Special Features	Used with C30 Lighting Contactor

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782116124701
Manufacturers Part Number	C320AMH2
UPC	782116124701

Taxonomies, Classifications, and Categories

Type	Mechanically held lighting contactor accessory
------	--

Packaging

Carton	1
Weight Per each	0.02



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

Commercial / Institutional Buildings / Structures - Commercial /
Institutional Buildings / Structures - Other

standard

UL Listed