



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## C600M12 C600 Kit Hoa SS Only

Eaton Corp

|                  |  |
|------------------|--|
| Catalog Number   | C600M12  |
| Manufacturer     | Eaton Corp   |
| Description      | Eaton Freedom Nema C600 Kit, C600 Kit, Hoa SS Only |
| Weight per unit  | 2.5 (lbs/each)                                     |
| Product Category | Starter Accessories                                |

### Dimensions and Weight

|        |   |
|--------|---|
| Depth  | 4 |
| Height | 4 |
| Width  | 1 |

### Descriptions

|                        |   |
|------------------------|---|
| Description            | C600 KIT HOA SS ONLY  |
| extra long description | ETN C600M12 C600 KIT, HOA SS ONLY   |
| Features               | Eaton's Freedom starters and contactors feature a compact, space-saving design, using state-of-the-art technology and the latest in high strength, impact and temperature resistant insulating materials. In addition to the bimetallic overload, Eaton also offers a series of electronic overload relay (C440) available as a standalone unit and assembled with Freedom contactor. |
| Long Description       | Eaton Freedom NEMA C600 kit, C600 KIT, HOA SS ONLY  |
| Product Type           | C600 Kit, Hoa SS Only   |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00786680147975 |
| Manufacturers Part Number | C600M12        |
| UPC                       | 786680147975   |

### Packaging

|                 |     |
|-----------------|-----|
| Carton          | 1   |
| Weight Per each | 2.5 |

### Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs |
| standard    | UL Listed  |