

## Features

- Enhanced J-Hook design reduces friction and offers less vertical compaction of cables
- Bendable locking tabs secure the J-Hooks in multiple configurations
- Available in 1, 2, 3, and 4 inch sizes for a greater number of cables
- Wide-base design maintains the bend radius of large diameter cable – 10G and shielded cable
- Interchangeable with a variety of accessories
- Easy to install and remove on-site
- Easy-to-assemble bracket simplifies J-Hook attachment for a variety of configurations
- Requires no special tools for installation
- Provides more headroom capability
- Accommodates a variety of attachment methods – threaded rod, wall mount, etc.
- Allows other trades to add on to the bottom of the J-Hook

The CADDY® CAT LINKS is the newest J-Hook support solution from ERICO® for use with a wide variety of cable, including larger-diameter cable and Cat. 6a and Cat. 7. Featuring a wide base with smooth, beveled edges, the versatile CADDY CAT LINKS provides a secure and stable installation and easily accommodates cables requiring a larger bend radius.

This environmentally friendly product is recyclable and uses less raw materials than tray systems because it is not a continuous pathway. And, unlike basket and cable tray, grounding is not necessary and less time, labor and materials are required in the construction of the total installed system.

To support a large amount of cable, trees can quickly and easily be assembled on site in many size combinations without requiring the use of special tools. The CADDY CAT LINKS is designed to accommodate high-performance cabling upgrades, which will help eliminate the need to replace your infrastructure as additional cable is added. Utilizing code-compliant materials and all-metal construction, the product meets worldwide standards and is ideal for use in multiple environments and applications.



## Recommended Cable Fill

	Ø (inch)	CSA (sq. in)	Cat. 5e & Fiber	Cat. 6	Cat. 6A min	Cat. 6A max	Cat. 7
Cable Ø	–	–	0.207	0.261	0.300	0.354	0.354
CAT16HP	1	1.07	20	15	10	7	7
CAT32HP	2	3.97	90	60	35	25	25
CAT48HP	3	9.26	200	150	80	60	60
CAT64HP	4	15.48	330	220	140	100	100

CSA = Cross-sectional area



## Order Information

Part No.	Description	Box Qty.	Weight/Box (lbs.)	Product Family
CAT16HP	1 inch J-Hook	50	8.60	MH
CAT32HP	2 inch J-Hook	50	13.70	MH
CAT48HP	3 inch J-Hook	25	10.88	MH
CAT64HP	4 inch J-Hook	25	12.93	MH
CATHPAN	Angle bracket with 3/16" Mounting Hole	50	1.70	MH
CATHPA4	Angle bracket with 1/4" Threaded Rod Mounting Hole	50	1.65	MH
CATHPA6	Angle bracket with 3/8" Threaded Rod Mounting Hole	50	1.65	MH
CATHPS4	Straight bracket with .282" Mounting Hole	50	1.05	MH
CATHPTM	Tree mounting bracket	50	2.70	MH
CATHP24	Hammer-on assembly for 1/4"-1/8" flange with 360° rotation	25	2.13	MH
CATHP58	Hammer-on assembly for 5/16"-1/2" flange with 360° rotation	25	2.25	MH
CATHP912	Hammer-on assembly for 1/2"-3/4" flange with 360° rotation	25	2.63	MH
CATHPBCB	Screw-on beam assembly for 1/8"-1/2" flange with 360° rotation	25	2.13	MH
CATHPBC200B	Screw-on beam assembly for 1/8"-5/8" flange with 360° rotation	25	3.60	MH
CATHP24SM	Hammer-on assembly for 1/8"-1/4" flange	50	2.60	MH
CATHP58SM	Hammer-on assembly for 5/16"-1/2" flange	50	2.75	MH
CATHP912SM	Hammer-on assembly for 1/2"-3/4" flange	25	1.50	MH
CATHPBC	Screw-on beam assembly for 1/8"-1/2" flange	50	3.50	MH
CATHPBC200	Screw-on beam assembly for 1/8"-5/8" flange	25	3.43	MH
CATHPAF14	Z purlin assembly for 1/16"-1/4" flange	50	3.10	MH
CATHPVF14	C purlin assembly for 1/16"-1/4" vertical flange	50	3.40	MH
CATHPESC	Easy strut assembly	50	2.20	MH
CATHP4Z34	Rod/flange assembly for #12 SWG - 1/4" wire or plain rod, 1/4" threaded rod & 1/8"-3/8" flange	50	2.30	MH
CATHP6Z34	Rod/flange assembly for 3/8" threaded rod & 3/8"-9/16" flange	50	2.25	MH
CATHPCD0B	Underfloor assembly for 3/4" round pedestal	25	1.78	MH
CATHPCD1B	Underfloor assembly for 7/8"-1" round pedestal or 3/4" square pedestal	25	2.40	MH
CATHPCD2B	Underfloor assembly for 7/8" square pedestal	25	2.85	MH
CATHPCD2.5B	Underfloor assembly for 1" square pedestal	25	3.05	MH
CAT16HPTS	Acoustical tee bar assembly	25	7.25	MH
CATHPLR	Cable Puller for CATHP	2	1.80	MH

WARNING – ERICO products shall be installed and used only as indicated in ERICO's product instruction sheets and training materials. Instruction sheets are available at [www.erico.com](http://www.erico.com) and from your ERICO customer service representative. Improper installation, misuse, misapplication or other failure to completely follow ERICO's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death.

Copyright ©2008 ERICO International Corporation. All rights reserved.  
CADDY, CADWELD, CRITEC, ERICO, ERIFLEX, ERITECH, and LENTON are registered trademarks of ERICO International Corporation.

Phone: 800-25-CADDY  
Fax: 800-462-4797  
[www.erico.com](http://www.erico.com)