

Specifications

Photo is representative

Eaton CCP15034CD RS

Eaton Crouse-Hinds series PowerMate CCP plug, 150A, 0.875-1.906", Three-wire, four-pole, Style 2, Copper-free aluminum, Reverse service, 600 Vac/250 Vdc

General specifications

PRODUCT NAME	Eaton Crouse-Hinds series PowerMate CCP plug
CATALOG NUMBER	CCP15034CD RS
UPC	662276277465
PRODUCT LENGTH/DEPTH	10.8 in
PRODUCT HEIGHT	4.13 in
PRODUCT WIDTH	4.13 in
PRODUCT WEIGHT	2.2 lb



Certifications and compliances

AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC
NEMA RATING	4X

Product specifications

AMPERAGE RATING	150A
GROUNDING TYPE	Style 2
CONFIGURATION	Three-wire, four-pole
CABLE DIAMETER	0.875-1.906"
VOLTAGE RATING	600 Vac/250 Vdc
MATERIAL	Copper-free aluminum
SPECIAL FEATURES	Reverse service

Resources

BROCHURES	PowerMate Drilling Pin and Sleeve Devices brochure
------------------	--

CATALOGS	PowerMate Drilling Pin and Sleeve Devices catalog page
CERTIFICATION REPORTS	PowerMate Drilling Pin and Sleeve Devices cUL certification (Plugs and Connectors)
	PowerMate Drilling Pin and Sleeve Devices UL certification (Plugs and Connectors)
INSTALLATION INSTRUCTIONS	IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices
	IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing
SPECIFICATIONS AND DATASHEETS	PowerMate Connectors
	Eaton Specification Sheet - CCP15034CD RS

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

