

Eaton CCP6034BC

Catalog Number: CCP6034BC

Eaton Crouse-Hinds series PowerMate CCP plug, 60A, 0.440-1.375", Three-wire, four-pole, Style 2, Copper-free aluminum, 600 Vac/250 Vdc

General specifications



| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton Crouse-Hinds series PowerMate CCP plug | CCP6034BC |
| | UPC |
| | 662276276604 |
| Product Length/Depth | Product Height |
| 8.17 in | 3.75 in |
| Product Width | Product Weight |
| 3.75 in | 2.2 lb |

Photo is representative

Certifications and compliances

Area classification

Ordinary/Non-Hazardous Locations

Standards type

NEC/CEC

NEMA Rating

4X

Product specifications

Amperage Rating

60A

Grounding type

Style 2

Configuration

Three-wire, four-pole

Cable diameter

0.440-1.375"

Voltage rating

600 Vac/250 Vdc

Material

Copper-free aluminum

Resources

3D CAD drawing package

[Eaton Crouse-Hinds CCP6034BC 3D drawing](#)

Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

Certification reports

[PowerMate Drilling Pin and Sleeve Devices cUL certification \(Plugs and Connectors\)](#)

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Plugs and Connectors\)](#)

Installation instructions

[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)

Specifications and datasheets

[PowerMate Connectors](#)

[Eaton Specification Sheet - CCP6034BC](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)