



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Type CCV Tenant Main Circuit Breaker

**CCV2125**

**UPC:**786685368399

### Dimensions:

- **Height:** 5.4 IN
- **Length:** 7.7 IN
- **Width:** 4.5 IN

**Weight:**2.9 LB

**Notes:**Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

### Warranties:

- Limited lifetime residential, 1 year commercial

### Specifications:

- **Amperage Rating:** 125A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CCV
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Used With:** Type ECC Unit Enclosures

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CCV2125](#)

### Certifications:

- UL 489

**Product compliance:** No Data





Powering Business Worldwide

pe.eaton.com

## Type CCV Tenant Main Circuit Breaker

CCV2125

UPC:786685368399

### Dimensions:

- **Height:** 5.4 IN
- **Length:** 7.7 IN
- **Width:** 4.5 IN

**Weight:**2.9 LB

**Notes:**Terminals-standard lugs (wire connectors) suitable for copper or aluminum wire.

### Warranties:

- Limited lifetime residential, 1 year commercial

### Specifications:

- **Amperage Rating:** 125A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CCV
- **Wire Size:** #2/0 AWG-300 kcmil Cu/Al
- **Used With:** Type ECC Unit Enclosures

### Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CCV2125](#)

### Certifications:

- UL 489

**Product compliance:** No Data

