

# Eaton CDR3033

Catalog Number: CDR3033

Eaton Crouse-Hinds series PowerMate CDR receptacle, 30A, Three-wire, three-pole, Style 1, Copper-free aluminum, 600 Vac/250 Vdc

Photo is representative

## General specifications

Product Name	Catalog Number
Eaton Crouse-Hinds series PowerMate CDR receptacle	CDR3033
	UPC
	662276277038
Product Length/Depth	Product Height
2.88 in	3.38 in
Product Width	Product Weight
3.38 in	2.2 lb



## Certifications and compliances

### Area classification

Ordinary/Non-Hazardous Locations

### Standards type

NEC/CEC

### NEMA Rating

4X

## Product specifications

### Amperage Rating

30A

### Grounding type

Style 1

### Configuration

Three-wire, three-pole

### Voltage rating

600 Vac/250 Vdc

### Material

Copper-free aluminum

## Resources

### 3D CAD drawing package

[Eaton Crouse-Hinds CDR3033 3D drawing](#)

### Brochures

[PowerMate Drilling Pin and Sleeve Devices brochure](#)

### Catalogs

[PowerMate Drilling Pin and Sleeve Devices catalog page](#)

### Certification reports

[PowerMate Drilling Pin and Sleeve Devices UL certification \(Receptacles\)](#)

### Installation instructions

[IF 1834 - PowerMate Pin and Sleeve Devices with Nested Bushing](#)  
[IF 1632 - 30, 60, 100 and 150A PowerMate Pin and Sleeve Devices](#)

### Specifications and datasheets

[PowerMate Connectors](#)  
[Eaton Specification Sheet - CDR3033](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)