



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CF32DTEIN841 32W 4 Pin Triple Tube Biax GX24Q-3 4100K Compact *Sylvania-Ledvance*

Catalog Number	CF32DTEIN841
Manufacturer	Sylvania-Ledvance
Description	Dulux 32W Triple Compact Fluorescent Amalgam Lamp With 4 Pin Base, 4100K Color Temperature, 82 Cri, For Use With Electronic and Dimming Ballasts, Ecologic
Weight per unit	0.2122 (lbs/each)
Product Category	Integrated Non-Ballasted Lamps

Features

amperage rating	Ballast Dependent
average life	16000
Base	GX24Q-3;GX24q-3
Lamp Type	DULUX T/E
lumens	2,400
Shape	T4X3
start type	ELECTRONIC RAPID START
total harmonic distortion	Ballast Dependent
Voltage Rating	Ballast Dependent
Wattage	32

Material, Color, and Finish

color temperature	4100
Finish	Phosphor Coated

Dimensions and Weight

Length	5.6
--------	-----

Descriptions

Description	32W 4 PIN TRIPLE TUBE BIAX GX24Q-3 4100K COMPACT
extra long description	SYL CF32DT/E/IN/841/ECO/20886 CF32D
Long Description	DULUX 32W triple compact fluorescent amalgam lamp with 4 pin base, 4100K color temperature, 82 CRI, for use with electronic and dimming ballasts, ECOLOGIC
Product Type	CF32DTEIN841ECO 50/CS 1/Sku

Manufacturer Information

Brand	OSRAM SYLVANIA
GTIN	00046135208867
Manufacturers Part Number	CF32DT/E/IN/841/ECO/20886
UPC	046135208867

Taxonomies, Classifications, and Categories

Category Description	Fluorescent
Type	Compact Fluorescent



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Availability

Status Inactive

Packaging

Carton 1

Package 50

Weight Per each 0.2122

Uses, Certifications, and Standards

Application Commercial/Residential