



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## CGB297 3/4" Dia Male Cord Grip (.750-.875)

*Crouse-Hinds*

Catalog Number	CGB297
Manufacturer	Crouse-Hinds
Description	Cord Gland, Steel With Zinc Electroplate and Chromate Finish Coat (Body, Gland Nut); Neoprene (Bushing) Material, CGB Model, 0.75 to 0.875 In Cable/Cord Size, 2.375 In Length, 1.78 In Diameter, Straight Male Connection, 3/4 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 0.55 LB
Weight per unit	0.5500 (lbs/each)
Product Category	Cable & Cord Grips

### Features

connection	Male NPT
dimensions	2.3800 IN X 1.7800 IN X 1.7800 IN

### Material, Color, and Finish

Finish	Zinc Electroplated With Chromate Coated
--------	---

### Dimensions and Weight

Size	3/4 in
------	--------

### Descriptions

Description	3/4" DIA MALE CORD GRIP (.750-.875)
extra long description	CRS-H CGB297 3/4 NPT MALE CORD/CAB
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

### Manufacturer Information

Brand	Eaton
GTIN	00782274745770
UPC	782274745770

### Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	10
Weight Per each	0.55

## Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C