



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



CGB6913 2" Dia Male Cord Grip (1.375-1.625)

Crouse-Hinds

Catalog Number	CGB6913
Manufacturer	Crouse-Hinds
Description	Cord Gland, Feraloy Iron Alloy With ElectroGalvanized and Aluminum Acrylic Paint (Body/Gland Nut);Neoprene (Bushing) Material, CGB Model, 1.375 to 1.625 In Cable/Cord Size, 3.438 In Length, 3 In Diameter, Straight Male Connection, 2 In Thread Size, -25 °C Operating Temperature, +40 °C Operating Temperature, 2.7 LB
Weight per unit	2.7 (lbs/each)
Product Category	Cable & Cord Grips

Features

connection	Male NPT
dimensions	3.4400 IN X 3.0000 IN X 3.0000 IN

Material, Color, and Finish

Finish	ElectroGalvanized With Aluminum Acrylic Painted
--------	---

Dimensions and Weight

Size	2 in
------	------

Descriptions

Description	2" DIA MALE CORD GRIP (1.375-1.625)
extra long description	CRS-H CGB6913 2 NPT MALE CORD/CAB F
Features	They are also listed for use with tray cable types TC, TC-ER, TC-ER-HLA, ITC, ITC-ER, ITC-HL, PLTC and PLTC-ER. When installed in accordance with NEC501.10(B)(4), CGB, CGD, CGE and CGFP non-armoured glands are suitable for use in Class I, Division 2 hazardous locations. Crouse-Hinds series CGB, CGD, CGE and CGFP non-armoured glands are installed to provide a means for passing a cord, unarmoured cable or flexible conduit into an enclosure. The glands form an environmental seal for cord or unarmoured round

Manufacturer Information

Brand	Eaton
GTIN	00782274140100
UPC	782274140100

Taxonomies, Classifications, and Categories

Category Description	CORD CONNECTORS & CORD GRIPS
Type	Cable gland



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	2
Weight Per each	2.7

Uses, Certifications, and Standards

Enclosure	Class I Div 2
standard	UL (CANADA AND US), CUL
Temperature Rating	-25 To 40 Deg C