

Eaton CH24B150E

Catalog Number: CH24B150E

CH 3/4-inch loadcenter, Main breaker, 150A, E, Copper, Ch8ef-combination, ch8es-surface, not included, NEMA 1, Metallic, 25 kAIC, CSR, 24, 24, Three-wire, Single-phase, #2/0 AWG-300 kcmil, Top/bottom

General specifications



Photo is representative

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CH24B150E
UPC	Product Length/Depth
782113097756	29.13 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
15 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Loadcenter can be overhead or underground fed by rotating the enclosure and trim 180 degrees.

Product specifications

Type

Main breaker

Amperage Rating

150 A

Bus material

Copper

Cover

Ch8ef-combination, ch8es-surface, not included

Main circuit breaker

CSR

Number of circuits

24

Number of spaces

24

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Feed type

Top/bottom

Box size

E

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

25 kAIC

Number of wires

3

Resources

Catalogs

Residential and Light Commercial, Load centers and Circuit Breakers, Volume 1 Tab 1

Multimedia

AFCI Educational Video

Specifications and datasheets

Eaton Specification Sheet - CH24B150E

Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)