

# Eaton CH42B200R

Catalog Number: CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH main breaker loadcenter	CH42B200R
<b>UPC</b>	<b>Product Length/Depth</b>
782113098227	37 in
<b>Product Height</b>	<b>Product Width</b>
5.19 in	14.31 in
<b>Product Weight</b>	<b>Warranty</b>
15.5 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 67	Furnished with hub closure plates.
UL 50	Loadcenter contains single insulated/bondable neutral.

## Product specifications

### Special features

Standard

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Main circuit breaker

CSR

### Number of circuits

42

### Number of spaces

42

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Feed type

Overhead

### Voltage rating

120/240 V

### Box size

K

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Catalogs

Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH42B200R

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton CH42B200R

Catalog Number: CH42B200R

Eaton CH main breaker loadcenters, Standard, Main breaker, 200 A, K, Copper, NEMA 3R, Metallic, 25 kAIC, CSR, 42, 42, Three-wire, Single-phase, #2 AWG-300 kcmil, Overhead, 120/240 V



Photo is representative

## General specifications

### Product Name

Eaton CH main breaker loadcenter

### Catalog Number

CH42B200R

### UPC

782113098227

### Product Length/Depth

37 in

### Product Height

5.19 in

### Product Width

14.31 in

### Product Weight

15.5 lb

### Warranty

Limited lifetime

### Certifications

UL 67

UL 50

### Catalog Notes

Furnished with hub closure plates.

Loadcenter contains single insulated/bondable neutral.

## Product specifications

### Special features

Standard

### Type

Main breaker

### Amperage Rating

200 A

### Bus material

Copper

### Main circuit breaker

CSR

### Number of circuits

42

### Number of spaces

42

### Phase

Single-phase

### Wire size

#2 AWG-300 kcmil

### Feed type

Overhead

### Voltage rating

120/240 V

### Box size

K

### Enclosure

NEMA 3R

### Enclosure material

Metallic

### Interrupt rating

25 kAIC

### Number of wires

3

## Resources

### Catalogs

Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1

### Multimedia

AFCI Educational Video

### Specifications and datasheets

Eaton Specification Sheet - CH42B200R

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)