



Powering Business Worldwide

pe.eaton.com



CH 3/4-inch main loadcenter

CH60BPN200N

UPC:786685425276

Dimensions:

- **Height:** 3.88 IN
- **Length:** 45 IN
- **Width:** 14.31 IN

Notes:Requires the use of type chnt breakers. Main breaker plug-on neutral loadcenter. 225A max.

Warranties:

- Limited lifetime

Specifications:

- **Special Features:** Plug-on neutral
- **Type:** Main breaker
- **Amperage Rating:** 200A
- **Box Size:** N
- **Bus Material:** Copper
- **Cover:** Ch8nf- combination, not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 35 kAIC
- **Main Circuit Breaker:** CSH
- **Number Of Circuits:** 60
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #2 AWG-300 kcmil
- **Voltage Rating:** 120/240V, 208Y/120, 240V

Supporting documents:

- [Type CH Circuit Breakers and Loadcenters](#)
- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [60 Circuit Plug-On Neutral Loadcenter](#)
- [Eaton Specification Sheet - CH60BPN200N](#)

Certifications:

- UL 67
- UL 50

Product compliance: No Data

© 2016 Eaton. All rights reserved.