

Eaton CHEC24L125E

Catalog Number: CHEC24L125E

Eaton CH surge loadcenter, Provision only, Convertible, 125 A, E, 24 Circuits, #6-4/0 AWG

General specifications



Photo is representative

Product Name	Eaton CH surge loadcenter	Catalog Number	CHEC24L125E
UPC	782116200146	Product Length/Depth	32 in
Product Height	3 in	Product Width	10 in
Product Weight	7 lb	Warranty	Limited lifetime
Certifications	UL Listed	Catalog Notes	Order Cover CHSUR8ES or CHSUR8EF separately. CHSPT2ULTRA and breaker not included

Product specifications

Special features

Provision only

Type

Main lug only

Amperage Rating

125 A

Bus material

Aluminum

Number of circuits

32

Number of spaces

32

Phase

Single-phase

Wire size

#6-4/0 AWG

Box size

E

Enclosure

NEMA 1

Interrupt rating

25 kAIC

Resources

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHEC24L125E](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)