

Specifications



Eaton CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits

Product specifications

SPECIAL FEATURES	Includes renovation terminal blocks
TYPE	Surge loadcenter
AMPERAGE RATING	225 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single phase
ENCLOSURE	NEMA 1
INTERRUPT RATING	25 kA

General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC32N225KRNSP
UPC	782116984183
PRODUCT LENGTH/DEPTH	37.5 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	22 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8KS or CHSUR8KF separately



Powering Business Worldwide

Specifications



Eaton CHEC32N225KRNSP

Eaton CH surge loadcenter, Includes renovation terminal blocks, Type CH surge ready loadcenter, 225 A, 32 Circuits

Product specifications

SPECIAL FEATURES	Includes renovation terminal blocks
TYPE	Surge loadcenter
AMPERAGE RATING	225 A
BUS MATERIAL	Aluminum
NUMBER OF CIRCUITS	32
NUMBER OF SPACES	32
PHASE	Single phase
ENCLOSURE	NEMA 3R
INTERRUPT RATING	25 kA

General specifications

PRODUCT NAME	Eaton CH surge loadcenter
CATALOG NUMBER	CHEC32N225KRNSP
UPC	782116984183
PRODUCT LENGTH/DEPTH	37.5 in
PRODUCT HEIGHT	4 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	22 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL Listed
CATALOG NOTES	Order Cover CHSUR8KS or CHSUR8KF separately



Powering Business Worldwide