



## CHF245 Type CHF BRKR 45A/2P 120/240V 10kaic

Eaton Corp

Catalog Number	CHF245
Manufacturer	Eaton Corp
Description	CH Style Load Center, 45 A, 120/240 V, #14 to #1 Awg Wire Size, 0.5 LB
Weight per unit	0.5000 (lbs/each)
Product Category	Single Phase Main Breaker Load

### Features

dimensions	1.5000 IN X 3.2000 IN X 2.6000 IN
interrupt rating	10
Poles	2

### Descriptions

Description	TYPE CHF BRKR 45A/2P 120/240V 10KAIC
extra long description	ETN CHF245 CHF BREAKER, 45A / 2P 12
Features	Eaton's residential CH circuit breakers provide premium overload protection. The Type CH circuit breakers trip to the OFF position, eliminating nuisance callbacks. The CHF family also includes a trip flag to differentiate between a trip and the breaker being turned off. The thermal-magnetic trip curve avoids nuisance tripping on mild overloads while reacting almost instantaneously to severe short-circuit conditions. Multiple breakers have an internal common trip connection to operate all poles simultaneous

### Manufacturer Information

GTIN	00786685545615
UPC	786685545615

### Taxonomies, Classifications, and Categories

Category Description	Loadcenter Plug In Breakers and Accessories
Type	Thermal magnetic circuit breakers

### Packaging

Carton	5
Package	25
Weight Per each	0.5

### Uses, Certifications, and Standards

Application	Generation - Renewable Energy - Alternative EnergyOtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper Converged Marine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	UL 489 HACR Rated