

# Eaton CHFEP120

Catalog Number: CHFEP120

Eaton CH GFCI circuit breaker, Ground fault equipment protector, Trip flag, 20 A, 10 kAIC, Single-pole, 120/240 V, CHFEP, Ground fault circuit interrupter, GFI, 30 mA



Photo is representative

## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton CH GFCI circuit breaker	CHFEP120
<b>UPC</b>	<b>Product Length/Depth</b>
786685627977	7.25 in
<b>Product Height</b>	<b>Product Width</b>
6.5 in	6.75 in
<b>Product Weight</b>	<b>Warranty</b>
3.33 lb	Limited lifetime
<b>Certifications</b>	<b>Catalog Notes</b>
UL 489	Switching Duty Rated, HACR Rated

## Product specifications

### Type

Ground fault equipment protector

### Special features

Trip flag

### Amperage Rating

20 A

### Voltage rating

120/240 V

### Circuit protection

Ground fault circuit interrupter

### Indicators

GFI

### Protection

30 mA

### Interrupt rating

10 kAIC

### Main circuit breaker

CHFEP

### Number of poles

Single-pole

## Resources

### Catalogs

Residential and Light Commercial, Metering Products, Volume 1 Tab 4

### Specifications and datasheets

Eaton Specification Sheet - CHFEP120

### Warranty guides

Eaton type CH circuit breaker limited warranty June 2024



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)