

# Eaton CHM1G7N7NS

Catalog Number: CHM1G7N7NS

Eaton pedestal mount metered, Metered-ring, Ground fault, Non-ground fault, Non-ground fault, Top, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI



## General specifications

### Product Name

Eaton pedestal mount metered

### Catalog Number

CHM1G7N7NS

### UPC

782114215586

### Product Length/Depth

31 in

### Product Height

7.8 in

### Product Width

10 in

### Product Weight

26 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Certifications

UL Listed file E163588

UL 231

## Product specifications

### Type

Metered-ring

### Utility approvals

AZ : Salt River Project (SRP)

### Circuit breaker position 1

Ground fault

### Circuit breaker position 2

Non-ground fault

### Circuit breaker position 3

Non-ground fault

### Receptacle center

NEMA 5-20R2GFI

### Receptacle left

NEMA 14-50R

### Receptacle right

NEMA 5-20R2GFI

### Feed type

Top

### Mounting

Surface

### Number of circuits

4

## Resources

### Catalogs

Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5

### Specifications and datasheets

Eaton Specification Sheet - CHM1G7N7NS



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia