

Eaton CHM1N7N7NSU

Catalog Number: CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V



Photo is representative

General specifications

Product Name

Eaton pedestal mount metered

Catalog Number

CHM1N7N7NSU

UPC

786685404264

Product Length/Depth

7.25 in

Product Height

31 in

Product Width

10 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Product specifications

Type

Metered-ring

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Resources

Catalogs

Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5

Specifications and datasheets

Eaton Specification Sheet - CHM1N7N7NSU



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton CHM1N7N7NSU

Catalog Number: CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V



Photo is representative

General specifications

Product Name

Eaton pedestal mount metered

Catalog Number

CHM1N7N7NSU

UPC

786685404264

Product Length/Depth

7.25 in

Product Height

31 in

Product Width

10 in

Product Weight

30 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Certifications

UL Listed file E163588

UL 231

Product specifications

Type

Metered-ring

Circuit breaker position 1

Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3

Non-ground fault

Receptacle center

NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Feed type

Bottom

Mounting

Surface

Number of circuits

4

Resources

Catalogs

[Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5](#)

Specifications and datasheets

[Eaton Specification Sheet - CHM1N7N7NSU](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)