

# Specifications



Photo is representative



## Eaton CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount metered
<b>CATALOG NUMBER</b>	CHM1N7N7NSU
<b>UPC</b>	786685404264
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	31 in
<b>PRODUCT WIDTH</b>	10 in
<b>PRODUCT WEIGHT</b>	30 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

## Product specifications

TYPE	Metered-ring
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHM1N7N7NSU</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications



Photo is representative



## Eaton CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V

### General specifications

<b>PRODUCT NAME</b>	Eaton pedestal mount metered
<b>CATALOG NUMBER</b>	CHM1N7N7NSU
<b>UPC</b>	786685404264
<b>PRODUCT LENGTH/DEPTH</b>	7.25 in
<b>PRODUCT HEIGHT</b>	31 in
<b>PRODUCT WIDTH</b>	10 in
<b>PRODUCT WEIGHT</b>	30 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed file E163588 UL 231

## Product specifications

TYPE	Metered-ring
CIRCUIT BREAKER POSITION 1	Non-ground fault
CIRCUIT BREAKER POSITION 2	Non-ground fault
CIRCUIT BREAKER POSITION 3	Non-ground fault
RECEPTACLE CENTER	NEMA 5-20R2GFI
RECEPTACLE LEFT	NEMA 14-50R
RECEPTACLE RIGHT	NEMA 5-20R2GFI
FEED TYPE	Bottom
MOUNTING	Surface
NUMBER OF CIRCUITS	4

## Resources

CATALOGS	<a href="#">Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - CHM1N7N7NSU</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



### Eaton Corporation plc

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

