Eaton CHM1N7N7NSU

Catalog Number: CHM1N7N7NSU

Eaton pedestal mount metered, Metered-ring, 50A, Non-ground fault, Non-ground fault, Non-ground fault, Bottom, Surface, Circuits: 4, NEMA 5-20R2GFI, NEMA 14-50R, NEMA 5-20R2GFI, 250V

General specifications

Product Name

Eaton pedestal mount metered

UPC 786685404264

Product Height 31 in

Product Weight 30 lb

Catalog Number CHM1N7N7NSU

Product Length/Depth 7.25 in

Product Width 10 in

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Photo is representative

Certifications UL Listed file E163588 UL 231



Product specifications

Туре

Metered-ring

Circuit breaker position 1 Non-ground fault

Circuit breaker position 2

Non-ground fault

Circuit breaker position 3 Non-ground fault

Receptacle center NEMA 5-20R2GFI

Receptacle left

NEMA 14-50R

Receptacle right

NEMA 5-20R2GFI

Feed type

Bottom

Mounting

Surface

Number of circuits

4



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2025 Eaton. All Right Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2025 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia

Resources

Catalogs

Residential and Light Commercial, Power Pedestals, Volume 1 Tab 5

Specifications and datasheets

Eaton Specification Sheet - CHM1N7N7NSU