

Eaton CHP14B100X1

Catalog Number: CHP14B100X1

Eaton CH main breaker loadcenters, Main breaker, 100 A, X1, Copper, X1, NEMA 1, Metallic, 10 kAIC, CH, 28, Single-pole, 14, Two hots, a neutral and a ground, Single-phase, #6-1/0 AWG, 120/240 V




Photo is representative

General specifications

Product Name	Catalog Number
Eaton CH main breaker loadcenter	CHP14B100X1
UPC	Product Length/Depth
786689055134	18.75 in
Product Height	Product Width
3.88 in	14.31 in
Product Weight	Warranty
11.1 lb	Limited lifetime
Certifications	
UL 50	
UL 67	

defaultTaxonomyAttributeLabel

Type

Main breaker

Amperage Rating

100 A

Bus material

Copper

Cover

X1

Main circuit breaker

CH

Number of circuits

28

Number Of Poles

Single-pole

Number of spaces

14

Phase

Single-phase

Wire size

#6-1/0 AWG

Voltage rating

120/240 V

Box size

X1

Enclosure

NEMA 1

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

Two hots, neutral and ground

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP14B100X1](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia