


Eaton CHP16L125X1

Catalog Number: CHP16L125X1

Eaton CH main lug loadcenters, PON, CH, 125A, X1, Copper, !, NEMA 1 indoor, Steel, 25 kAIC, 32, Single-pole, 16, Three-wire, Single-phase, 120/240 V, #6-2/0 AWG



General specifications

Product Name	Catalog Number
Eaton CH main lug loadcenter	CHP16L125X1
UPC	Product Length/Depth
786689059705	18.75 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Warranty
9.9 lb	Limited lifetime
Certifications	Catalog Notes
UL 50 UL 67	Purchase Size X1 cover seperately

Product specifications

Special features

PON

Type

CH

Amperage Rating

125 A

Bus material

Copper

Number of circuits

32

Number Of Poles

Single-pole

Number of spaces

16

Phase

Single-phase

Voltage rating

120/240 V

Wire size

#8-1/0 AWG Cu

Box size

X1

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

25 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP16L125X1](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)