

# Specifications

Photo is representative



## Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CHP24L150R
<b>UPC</b>	786689058623
<b>PRODUCT LENGTH/DEPTH</b>	29 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

### Product specifications

<b>SPECIAL FEATURES</b>	Cover included
<b>TYPE</b>	Main Lug
<b>AMPERAGE RATING</b>	150
<b>BUS MATERIAL</b>	Copper
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF CIRCUITS</b>	48
<b>NUMBER OF SPACES</b>	24
<b>PHASE</b>	Single phase
<b>BOX SIZE</b>	X5
<b>ENCLOSURE</b>	NEMA 3R
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25
<b>NUMBER OF WIRES</b>	3



# Specifications

Photo is representative



## Eaton CHP24L150R

Eaton CH main lug loadcenters, Cover included, Main Lug Only, 150A, X5, Copper, NEMA 3R, Metallic, Overhead, 48, 24, Three-wire, Single-phase

### General specifications

<b>PRODUCT NAME</b>	Eaton CH main lug loadcenter
<b>CATALOG NUMBER</b>	CHP24L150R
<b>UPC</b>	786689058623
<b>PRODUCT LENGTH/DEPTH</b>	29 in
<b>PRODUCT HEIGHT</b>	5.19 in
<b>PRODUCT WIDTH</b>	14.31 in
<b>PRODUCT WEIGHT</b>	26 lb
<b>WARRANTY</b>	Limited lifetime
<b>CERTIFICATIONS</b>	UL 67 UL 50
<b>CATALOG NOTES</b>	Suitable for use as service equipment when not more than six service disconnecting mains are provided or when not used as a lighting and appliance panelboard. Rainproof panels are furnished with hub closure plates. For rainproof hubs.

### Product specifications

<b>SPECIAL FEATURES</b>	Cover included
<b>TYPE</b>	Main Lug
<b>AMPERAGE RATING</b>	150
<b>BUS MATERIAL</b>	Copper
<b>FEED TYPE</b>	Overhead
<b>NUMBER OF CIRCUITS</b>	48
<b>NUMBER OF SPACES</b>	24
<b>PHASE</b>	Single phase
<b>BOX SIZE</b>	X5
<b>ENCLOSURE</b>	NEMA 3R
<b>ENCLOSURE MATERIAL</b>	Metallic
<b>INTERRUPT RATING</b>	25
<b>NUMBER OF WIRES</b>	3

