

Eaton CHP24L150X5

Catalog Number: CHP24L150X5

Eaton CH main lug only panel, PON,150A,X5,Copper bus,,NEMA 1 indoor,Steel,10 kAIC,48 circuits,24 spaces,Single-phase,120/240 V,#4 AWG-300 kcmil



General specifications

Product Name	Catalog Number
Eaton CH spa panel	CHP24L150X5
UPC	Product Length/Depth
786689054274	29 in
Product Height	Product Width
4 in	14.3 in
Product Weight	Certifications
15.4 lb	UL 67

Catalog Notes

Purchase Size X5 Cover Separately

Product specifications

Special features

PON

Type

CH

Amperage Rating

150 A

Bus material

Copper

Number of circuits

48

Number of spaces

24

Phase

Single-phase

Voltage rating

120/240 V

Box size

X5

Enclosure

NEMA 1

Enclosure material

Steel

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP24L150X5](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)