

Eaton CHP32N200R

Catalog Number: CHP32N200R

Eaton CH plug-on neutral loadcenter, 200A, convertible, 32 spaces, NEMA 3R



General specifications

Product Name	Catalog Number
Eaton CH convertible loadcenter	CHP32N200R
UPC	Product Length/Depth
786689059637	34.13 in
Product Height	Product Width
5.19 in	14.31 in
Product Weight	Warranty
35 lb	Limited lifetime
Certifications	
UL 50	
UL 67	

Product specifications

Special features

Standard

Type

Convertible

Amperage Rating

200 A

Bus material

Copper

Feed type

Overhead

Main circuit breaker

CSR

Number of circuits

64

Number of spaces

32

Phase

Single-phase

Wire size

#2/0 AWG-300 kcmil

Box size

X6

Enclosure

NEMA 3R

Enclosure material

Metallic

Interrupt rating

10 kAIC

Number of wires

3

Resources

Brochures

[Loadcenters and Circuit Breakers](#)

Multimedia

[AFCI Educational Video](#)

Specifications and datasheets

[Eaton Specification Sheet - CHP32N200R](#)

Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)